



Stainless Steel W Die, Index 167, 207, 211,
,256, 568

By Burndy
Catalog # [W167](#)

6T W Die, Index 167, 207, 211, 256, 568



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Die Index 167, 207, 211, ,256, 568

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Weight	0.12 lb.

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Die Index	167
Die Type	W Die
UPC	781810440315
Type	Die
Material	Stainless Steel
UPC 12 Digit	781810440315
UPC 14 Digit GTIN	00781810440315

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)