



BURNDY

Stainless Steel W Die, Index 249

By Burndy
Catalog # [W249](#)
6T W Die, Index 249



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Die Index 249

Application

Crimping

Specifications

Standards - RoHS Compliance Status
EX
EU RoHS Indicator
Yes

Conductor

Crimping Ranges
Aluminum: # 250 Kcmil

Dimensions

Weight
0.13 lb.

Force Related

Crimp Force Capacity
6 ton

General

Application - For Use On
Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Die Index
249
Die Type
W Die
UPC
781810440469
Type
W-Die for Hydraulic Crimping Tools (set)
Construction Material - Main
Stainless Steel
UPC 12 Digit
781810440469
UPC 14 Digit GTIN
00781810440469

Logistics

Package Contents
Die only
Pallet Quantity
11520
Carton Quantity
80

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY_CA-W249-SPEC-EN | REV 5/2026