



Stainless Steel Cutter W Die, Cuts #4 AWG-4/0 AWG Copper, Aluminum and ACSR

By Burndy
Catalog # [W28K](#)

6T W Die Cutter, #4-4/0 AWG ACSR, CU/AL



Features

- Durable Stainless Steel Material
- Twin W Style
- Cuts #4-4/0 AWG CU/AL/ACSR

Application

Cutting

Specifications

Standards - RoHS Compliance Status	EX
EU RoHS Indicator	Yes

Dimensions

Weight	0.14 lb.
--------	----------

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Die Type	W Die
UPC	781810440223
Type	Dies
UPC 12 Digit	781810440223
UPC 14 Digit GTIN	00781810440223

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)