



Stainless Steel W Die, White, Index 17, V Profile

By Burndy
Catalog # [W30VT](#)

6T W Die (V), 300 kcmil, White, Index 17



Features

- Durable Stainless Steel Material
- Oblong Crimp
- Twin W-VT Style
- Color Code: White
- Die Index 17

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Weight	0.12 lb.

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Color Code	White
Die Index	17
Die Type	W Die
UPC	781810037690
Type	Die
Material	Stainless Steel
UPC 12 Digit	781810037690
UPC 14 Digit GTIN	00781810037690

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)