



Stainless Steel W Die, Brown, Index 20, V Profile

By Burndy
Catalog # [W34VT](#)



6T W Die (V) 500 kcmil CU Brown Index 20

Features

- Durable Stainless Steel Material
- Oblong Crimp
- Twin W-VT Style
- Color Code: Brown
- Die Index 20

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Weight	0.10 lb.

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Color Code	Brown
Die Index	20
Die Type	W Die
UPC	781810037720
Type	Die
UPC 12 Digit	781810037720
UPC 14 Digit GTIN	00781810037720

Logistics

Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)