



Stainless Steel Non-Butting W Die, 600 kcmil CU, Green, Index 22

By Burndy
Catalog # [W36RT](#)

6T W Die, 600 kcmil CU, Green, Index 22



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Color Code: Green
- Die Index 22

Application

Crimping

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Weight	0.11 lb.
--------	----------

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Color Code	Green
Die Index	22
Die Type	W Die
UPC	781810363638
Type	Die
Material	Stainless Steel
UPC 12 Digit	781810363638
UPC 14 Digit GTIN	00781810363638

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)