

WAD33635, WEJTAP Applied In-Line Disconnect Switch

By Burndy

Catalog # [WAD33635](#)

MAX RANGE: .642 - .723 ACSR: 266.8 (26/7), 336.4 (18/1), (26/7)
AAC: 336, 350, 397.5, 477 COMPACT 35 kV, 200 BIL.

Features

- WEJTAP In-Line Disconnect utilizes proven WEJTAP technology in combination with industry standard components to provide reliable performance of switch applications
- Designed for use in gloving and hot stick applications in conjunction with an industry standard load break tool
- Dual insulators minimize the switch movement during opening and closing of the blade
- In-Line Disconnect is removable and reusable

General

Catalog Number	WAD33635
Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810462157
UPC 14 Digit GTIN	00781810462157

Dimensions

Dimension - B Length fraction	22-2/5 in
Dimension - B Length inch	22.4 in
Dimension - Length Overall inch	54 in

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 5005 Size Range	312.8 (19) kcmil-394.5 (19) kcmil
Conductor - AAAC 6201 Size	312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 6201 Size Range	312.8 (19) kcmil-394.5 (19) kcmil



Conductor - ACSR Str Size	266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	266.8 (26/7) Owl kcmil-336.4 (30/7) Oriole kcmil
Conductor - AL Str Size	336 kcmil;350 kcmil;397 kcmil
Conductor - AL Str Size Range	336 kcmil-397 kcmil
Conductor Type	• AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	37

Product Assets

[3D Models - WAD33635_MODEL-STEP](#)
[3D Models - WAD33635_MODEL-IGES](#)
[3D Models - WAD33635_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10083326](#)
[Specifications - WAD33635](#)