



WAD4015, WEJTAP Applied In-Line Disconnect Switch

By Burndy
Catalog # [WAD4015](#)

BURNNDY® WEJTAP™ In-Line Disconnect; Features: KV/BIL Ratings- 15 kV/110 kV Bil; For securing the switch to the distribution line in tension applications

Features

- WEJTAP In-Line Disconnect utilizes proven WEJTAP technology in combination with industry standard components to provide reliable performance of switch applications
- Designed for use in gloving and hot stick applications in conjunction with an industry standard load break tool
- Dual insulators minimize the switch movement during opening and closing of the blade
- In-Line Disconnect is removable and reusable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	30.58 (7) kcmil
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil
Conductor - AAAC 6201 Size	30.58 (7) kcmil
Conductor - AL Str Size	• 4/0 AWG • 250 kcmil • 266 kcmil
Conductor - AAAC 5005 Size	30.58 (7) kcmil
Conductor - AL Str Size Range	4/0 AWG-266 kcmil
Conductor Type	• AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	• 4/0 (6/1) Penguin AWG



Conductor - ACSR Str Size Range	• 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil
	4/0 (6/1) Penguin AWG-266.8 (18/1) Waxwing kcmil

Current

Current Rating	900 A
----------------	-------

Dimensions

Length	45 in
--------	-------

Force Related

Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs

General

Insulator Type	Silicon
Trade Name	WEJTAP™
UPC	781810489161
Material	Aluminum Alloy
UPC 12 Digit	781810489161
UPC 14 Digit GTIN	00781810489161

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)