

WAD47735, WEJTAP Applied In-Line Disconnect Switch

By Burndy
Catalog # [WAD47735](#)

BURNDY® WEJTAP™ In-Line Disconnect; Features: KV/BIL Ratings- 15 kV/110 kV Bil; For securing the switch to the distribution line in tension applications

Features

- WEJTAP In-Line Disconnect utilizes proven WEJTAP technology in combination with industry standard components to provide reliable performance of switch applications
- Designed for use in gloving and hot stick applications in conjunction with an industry standard load break tool
- Dual insulators minimize the switch movement during opening and closing of the blade
- In-Line Disconnect is removable and reusable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	UI
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	465.4 (19) kcmil
Conductor - AAAC 6201 Size Range	465.4 (19) kcmil
Conductor - AAAC 6201 Size	465.4 (19) kcmil
Conductor - AL Str Size	• 450 kcmil • 477 kcmil • 500 kcmil
Conductor - AAAC 5005 Size	465.4 (19) kcmil
Conductor - AL Str Size Range	450 kcmil-500 kcmil
Conductor Type	• AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	• 397.5 (18/1) Chickadee kcmil



Conductor - ACSR Str Size Range	• 397.5 (24/7) Brant kcmil • 397.5 (26/7) Ibis kcmil • 397.5 (30/7) Larkspur kcmil • 477.0 (18/1) Pelican kcmil
	397.5 (18/1) Chickadee kcmil-477.0 (18/1) Pelican kcmil

Current

Current Rating	900 A
----------------	-------

Dimensions

Length	54 in
Dimension - B Length fraction	22-2/5 in
Dimension - B Length inch	22.4 in
Dimension - Length Overall inch	54 in

Force Related

Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs

General

Insulator Type	Silicon
Trade Name	WEJTAP™
UPC	781810462188
Material	Aluminum Alloy
UPC 12 Digit	781810462188
UPC 14 Digit GTIN	00781810462188

Logistics

Pallet Quantity	37
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)