



WAD55635, WEJTAP Applied In-Line Disconnect Switch

By Burndy
Catalog # [WAD55635](#)

BURNDY® WEJTAP™ In-Line Disconnect; Features: KV/BIL Ratings- 35 kV/200 kV Bil; For securing the switch to the distribution line in tension applications

Features

- WEJTAP In-Line Disconnect utilizes proven WEJTAP technology in combination with industry standard components to provide reliable performance of switch applications
- Designed for use in gloving and hot stick applications in conjunction with an industry standard load break tool
- Dual insulators minimize the switch movement during opening and closing of the blade
- In-Line Disconnect is removable and reusable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	559.5 (19) kcmil
Conductor - AAAC 6201 Size Range	559.5 (19) kcmil
Conductor - AAAC 6201 Size	559.5 (19) kcmil
Conductor - AL Str Size	• 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil
Conductor - AAAC 5005 Size	559.5 (19) kcmil
Conductor - AL Str Size Range	477 kcmil-556 kcmil
Conductor Type	• AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size



Conductor - ACSR Str Size	• AL C Str-Size • 477.0 (26/7) Hawk kcmil • 477. (30/7) Hen kcmil
Conductor - ACSR Str Size Range	477.0 (26/7) Hawk kcmil-477. (30/7) Hen kcmil

Current

Current Rating	900 A
----------------	-------

Dimensions

Length	54 in
Dimension - B Length fraction	22-2/5 in
Dimension - B Length inch	22.4 in
Dimension - Length Overall inch	54 in

Force Related

Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs

General

Insulator Type	Silicon
Trade Name	WEJTAP™
UPC	781810462249
Material	Aluminum Alloy
UPC 12 Digit	781810462249
UPC 14 Digit GTIN	00781810462249

Logistics

Minimum Pack Quantity	1
Pallet Quantity	37
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)