



WAD795-35, WEJTAP Applied In-Line Disconnect Switch

By Burndy
Catalog # [WAD795-35](#)

MAX RANGE: .953 - 1.040 ACSR: 556 (24/7), (26/7), (30/7)
795 (36/1) AAC: 795 (37 STR, 61 STR) 15 kV, 110 BIL.



General

Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810489192
UPC 12 Digit	7818104891922

Dimensions

Dimension - B Length fraction	22-2/5 in
Dimension - B Length inch	22.4 in
Dimension - Length Overall inch	54 in

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	740.8 (37) kcmil
Conductor - AAAC 5005 Size Range	740.8 (37) kcmil
Conductor - AAAC 6201 Size	740.8 (37) kcmil
Conductor - AAAC 6201 Size Range	740.8 (37) kcmil
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil; 556.5 (26/7) Dove kcmil; 556.5 (30/7) Eagle kcmil; 605 (24/7) Peacock kcmil; 605 (26/7) Squab kcmil; 605 (30/19) Teal kcmil; 636 (24/7) Rook kcmil; 636 (26/7) Grosbeak kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-636 (26/7) Grosbeak kcmil
Conductor - AL Str Size	795 kcmil
Conductor - AL Str Size Range	795 kcmil
Conductor Type	• AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	37

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10083326](#)



A proud member of the Hubbell Family.