



Stainless Steel W Die, Index BG

By Burndy
Catalog # [WBG](#)

6T W Die, Index BG



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Die Index BG

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	• Copper: #6 AWG - 4/0 AWG • Aluminum: #6 AWG - 1/0 AWG • ACSR: #6 AWG - 1/0 AWG
-----------------	--

Dimensions

Weight	0.17 lb.
--------	----------

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Die Index	BG
Die Type	W Die
UPC	781810440056
Type	W-Die for Hydraulic Crimping Tools
Construction Material - Main	Stainless Steel
UPC 12 Digit	781810440056
UPC 14 Digit GTIN	00781810440056

Logistics

Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	120

Product Assets

[Catalog \[English\]](#)