




WCB13PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCB13PB](#)

WEJTAP Connector , 0.568 - 0.364 (Run), 0.258 - 0.204 (Tap),
With Blue Power Booster Assembly



Features

- WEJTAP Connector
- Blue Power Booster included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Run	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - AL Str Tap Range	4 AWG
Conductor - AL Str Tap	4 AWG
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penguin AWG
Conductor - ACSR Str Run	• 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penguin AWG

Conductor - ACSR Str Tap Range	5 (6/1) Thrush AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Tap	• 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.04 in
Dimension - F Width Center to Center inch	1.64 in

General

Color	Blue
Trade Name	WEJTAP™
UPC	781810870037
Material	Aluminum
UPC 12 Digit	781810870037
UPC 14 Digit GTIN	00781810870037

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalog \[English\]](#)