



# WCB18PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCB18PB](#)

Wejtap connector installed with blue booster,.364-.572 (Tap)

### Features

- WEJTAP Connector
- Blue Power Booster included

### Specifications

|                              |    |
|------------------------------|----|
| Standards - RoHS Compliance  | NC |
| Status                       |    |
| Certification - CSA Approved | No |

### Conductor

|                                |                                                                                                                                         |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range   | 1/0 AWG-4/0 AWG                                                                                                                         |
| Conductor - AL Str Run         | <ul style="list-style-type: none"><li>• 1/0 AWG</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li></ul>                         |
| Conductor - AL Str Tap Range   | 1/0 AWG-4/0 AWG                                                                                                                         |
| Conductor - AL Str Tap         | <ul style="list-style-type: none"><li>• 1/0 AWG</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li></ul>                         |
| Conductor Type                 | <ul style="list-style-type: none"><li>• ACSR C Str-Run</li><li>• AL C Str-Run</li><li>• ACSR C Str-Tap</li><li>• AL C Str-Tap</li></ul> |
| Conductor - ACSR Str Run Range | 1/0 (6/1) Raven AWG-4/0 (6/1) Penguin AWG                                                                                               |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>• 1/0 (6/1) Raven AWG</li><li>• 2/0 (6/1) Quail AWG</li><li>• 3/0 (6/1) Pigeon AWG</li></ul>      |

|                                |                                                                                                                                                                    |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - ACSR Str Tap Range | <ul style="list-style-type: none"><li>• 4/0 (6/1) Penguin AWG</li><li>1/0 (6/1) Raven AWG-4/0 (6/1) Penguin AWG</li></ul>                                          |
| Conductor - ACSR Str Tap       | <ul style="list-style-type: none"><li>• 1/0 (6/1) Raven AWG</li><li>• 2/0 (6/1) Quail AWG</li><li>• 3/0 (6/1) Pigeon AWG</li><li>• 4/0 (6/1) Penguin AWG</li></ul> |

### Configuration

|                |     |
|----------------|-----|
| Connector Type | Tap |
|----------------|-----|

### Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - G inch                        | 1.04 in |
| Dimension - F Width Center to Center inch | 1.64 in |

### General

|                   |                |
|-------------------|----------------|
| Color             | Blue           |
| Trade Name        | WEJTAP™        |
| UPC               | 781810870082   |
| Material          | Aluminum       |
| UPC 12 Digit      | 781810870082   |
| UPC 14 Digit GTIN | 00781810870082 |

### Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

### Product Assets

[Catalog \[English\]](#)