



WCB19, WEJTAP Connector

By Burndy
Catalog # [WCB19](#)

Wejtap connector installed with blue booster, .364-.564 (Run),
.379-.572 (Tap)

Features

- WEJTAP Connector installed with Blue Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Run	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Conductor - AL Str Tap Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Conductor - ACSR Str Run Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penguin AWG
Conductor - ACSR Str Run	1/0 (6/1) Raven AWG 2/0 (6/1) Quail AWG 3/0 (6/1) Pigeon AWG 4/0 (6/1) Penguin AWG
Conductor - ACSR Str Tap Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penguin AWG

Conductor - ACSR Str Tap	1/0 (6/1) Raven AWG 2/0 (6/1) Quail AWG 3/0 (6/1) Pigeon AWG 4/0 (6/1) Penguin AWG
--------------------------	--

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.04 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.64 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810872901
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810872901
UPC 14 Digit GTIN	00781810872901

Logistics

Minimum Pack Quantity	25
Pallet Quantity	2100
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)