




WCB25PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCB25PB](#)



WEJTAP Connector , 0.650 - 0.532 (Run), 0.562 - 0.364 (Tap),
With Blue Power Booster Assembly

Features

- WEJTAP Connector
- Blue Power Booster included

Specifications

Standards - RoHS Compliance Status	NC
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	250 kcmil-300 kcmil
Conductor - AL Str Run	• 250 kcmil • 266 kcmil • 300 kcmil
Conductor - AL Str Tap Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Run	• 4/0 (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil

Conductor - ACSR Str Tap Range	• 266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap	• 1/0 (6/1) Raven AWG-3/0 (6/1) Pigeon AWG • 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.05 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.89 in
Package Width	0.000 in

General

Color	Blue
Trade Name	WEJTAP™
UPC	781810870150
Material	Aluminum
UPC 12 Digit	781810870150
UPC 14 Digit GTIN	00781810870150

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalog \[English\]](#)