



WCB44, WEJTAP Connector

By Burndy
Catalog # [WCB44](#)

Wejtap Assembly , Installed With Blue Booster,Run:.684-.600,
Tap:.562-.364

Features

- WEJTAP Connector installed with Blue Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Run	• 300 kcmil • 336 kcmil • 350 kcmil
Conductor - AL Str Tap Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run	• 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil • 266.8 (26/7) Partridge kcmil • 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil

Conductor - ACSR Str Tap Range	1/0 (6/1) Raven AWG-3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Tap	• 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.1 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	2 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810873601
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810873601
UPC 14 Digit GTIN	00781810873601

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1750
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)