



WCB45, WEJTAP Connector

By Burndy
Catalog # [WCB45](#)

Wejtap Assembly, 0.684-0.600 (Run), 0.562-0.409 (Tap),
Installed With Blue Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Run	300 kcmil 336 kcmil 350 kcmil
Conductor - AL Str Tap Range	2/0 AWG-4/0 AWG
Conductor - AL Str Tap	2/0 AWG 3/0 AWG 4/0 AWG
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil 266.8 (26/7) Owl kcmil 266.8 (26/7) Partridge kcmil 300.0 (26/7) Ostrich kcmil 336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap Range	2/0 (6/1) Quail AWG-3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Tap	2/0 (6/1) Quail AWG

- 3/0 (6/1) Pigeon AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.1 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	2 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810873656
Material	Aluminum
UPC 12 Digit	781810873656
UPC 14 Digit GTIN	00781810873656

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1750
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)