




WCB46PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCB46PB](#)

Wejtap connector installed with blue booster, .600-.684 Run, .460-.592 (Tap)



Features

- WEJTAP Connector
- Blue Power Booster included

Specifications

Standards - RoHS Compliance Status	NC
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Run	• 300 kcmil • 336 kcmil • 350 kcmil
Conductor - AL Str Tap Range	3/0 AWG-250 kcmil
Conductor - AL Str Tap	• 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run	• 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil • 266.8 (26/7) Partridge kcmil • 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap Range	2/0 (6/1) Quail AWG-4/0 (6/1) Penguin AWG

Conductor - ACSR Str Tap	• 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penguin AWG
--------------------------	--

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.1 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	2 in
Package Width	0.000 in

General

Color	Blue
Trade Name	WEJTAP™
UPC	781810870259
Material	Aluminum
UPC 12 Digit	781810870259
UPC 14 Digit GTIN	00781810870259

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalog \[English\]](#)