

WCBY39R4N, WEJTAP Terminal

By Burndy
Catalog # [WCBY39R4N](#)



Al Wedge Tap Power Plug Terminal, 266.8 - 556.5 kcmil ACSR,
336.4 - 636 kcmil AAC/ASC, 4 Pad Holes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor - ACSR Str Size Range	• 556.5 (24/7) Parakeet
	• 556.5 (26/7) Dove
	• 556.5 (30/7) Eagle
	266.8 (18/1) Waxwing-556.5 (30/7) Eagle

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Tap

Dimensions

Dimension - Pad Width inch	3.75 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - D inch	3.5 in
Dimension - N inch	1 in
Dimension - Hole Size inch	0.56 in

General

Trade Name	WEJTAP™
UPC	781810871362
Material	Aluminum
UPC 12 Digit	781810871362
UPC 14 Digit GTIN	00781810871362

Logistics

Minimum Pack Quantity	1
Pallet Quantity	432
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)

Conductor

Conductor - AL Str Size	• 336.4
	• 350
	• 397.5
	• 400
	• 450
	• 477
	• 500
	• 550
	• 556.5
	• 600
	• 636
	• 650
Conductor - AL Str Size Range	336.4-650
Conductor - ACSR Str Size	• 266.8 (18/1) Waxwing
	• 266.8 (26/7) Owl
	• 266.8 (26/7) Partridge
	• 300.0 (26/7) Ostrich
	• 336.4 (18/1) Merlin
	• 336.4 (26/7) Linnet
	• 336.4 (30/7) Oriole
	• 397.5 (18/1) Chickadee
	• 397.5 (24/7) Brant
	• 397.5 (26/7) Ibis
	• 397.5 (30/7) Larkspur
	• 477.0 (18/1) Pelican
	• 477.0 (24/7) Flicker
	• 477.0 (26/7) Hawk
	• 477.0 (30/7) Hen