



WCR29PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCR29PB](#)

WEJTAP Connector, 0.398 - 0.257 (Run), 0.398 - 0.257 (Tap),
With Red Power Booster Assembly

Features

- WEJTAP Connector
- Red Power Booster Included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	2 AWG-1/0 AWG
Conductor - AL Str Run	• 2 AWG • 1 AWG • 1/0 AWG
Conductor - AL Str Tap Range	2 AWG-1/0 AWG
Conductor - AL Str Tap	• 2 AWG • 1 AWG • 1/0 AWG
Conductor - ACSR Str Run Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Run	• 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG

Conductor - ACSR Str Tap	• 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG
--------------------------	---

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Dimension - F Width Center to Center inch	1.40 in

General

Color	Red
Trade Name	WEJTAP™
UPC	781810870365
Material	Aluminum
UPC 12 Digit	781810870365
UPC 14 Digit GTIN	00781810870365

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalog \[English\]](#)