



WCR30, WEJTAP Connector

By Burndy
Catalog # [WCR30](#)

Wejtap Assembly, Installed With Red Booster, Sum of Diameters:
.649 (Max), .516 (Min)



Features

- WEJTAP Connector installed with Red Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	2 AWG-1/0 AWG
Conductor - AL Str Run	2 AWG 1 AWG 1/0 AWG
Conductor - AL Str Tap Range	4 AWG-2 AWG
Conductor - AL Str Tap	4 AWG 3 AWG 2 AWG
Conductor - ACSR Str Run Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Run	4 (7/1) Swanate AWG 3 (6/1) Swallow AWG 2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG 1 (6/1) Robin AWG 1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	5 (6/1) Thrush AWG-2 (7/1) Sparate AWG

Conductor - ACSR Str Tap	5 (6/1) Thrush AWG 4 (6/1) Swan AWG 4 (7/1) Swanate AWG 3 (6/1) Swallow AWG 2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG
--------------------------	---

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.40 in
Package Width	0.000 in

General

Color	Red
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810872055
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810872055
UPC 14 Digit GTIN	00781810872055

Logistics

Minimum Pack Quantity	25
Pallet Quantity	2800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)