



WCR30PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCR30PB](#)

Wejtap connector installed with red booster, .257-.398 (Run), .206-.325 (Tap)

Features

- WEJTAP Connector
- Red Power Booster Included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	2 AWG-1/0 AWG
Conductor - AL Str Run	• 2 AWG • 1 AWG • 1/0 AWG
Conductor - AL Str Tap Range	4 AWG-2 AWG
Conductor - AL Str Tap	• 4 AWG • 3 AWG • 2 AWG
Conductor - ACSR Str Run Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Run	• 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	5 (6/1) Thrush AWG-2 (7/1) Sparate AWG



Conductor - ACSR Str Tap	• 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
--------------------------	---

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Dimension - F Width Center to Center inch	1.40 in

General

Color	Red
Trade Name	WEJTAP™
UPC	781810870372
Material	Aluminum
UPC 12 Digit	781810870372
UPC 14 Digit GTIN	00781810870372

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalog \[English\]](#)