



WCR31, WEJTAP Connector

By Burndy
Catalog # [WCR31](#)

Wejtap connector installed with red booster, .257-398 (Run), .162-.258 (Tap)



Features

- WEJTAP Connector installed with Red Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	2 AWG-1/0 AWG
Conductor - AL Str Run	2 AWG 1 AWG 1/0 AWG
Conductor - AL Str Tap Range	8 AWG-3 AWG
Conductor - AL Str Tap	8 AWG 6 AWG 4 AWG 3 AWG
Conductor - ACSR Str Run Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Run	4 (7/1) Swanate AWG 3 (6/1) Swallow AWG 2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG 1 (6/1) Robin AWG 1/0 (6/1) Raven AWG

Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG 5 (6/1) Thrush AWG 4 (6/1) Swan AWG 4 (7/1) Swanate AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.40 in
Package Width	0.000 in

General

Color	Red
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810872109
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810872109
UPC 14 Digit GTIN	00781810872109

Logistics

Pallet Quantity	2800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)