

WCR33, WEJTAP Connector

By Burndy
Catalog # [WCR33](#)

Wejtap connector installed with red booster, .169-.258 (Run),
.162-.230 (Tap)



Features

- WEJTAP Connector installed with Red Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	8 AWG-4 AWG
Conductor - AL Str Run	8 AWG 6 AWG 4 AWG
Conductor - AL Str Tap Range	8 AWG-4 AWG
Conductor - AL Str Tap	8 AWG 6 AWG 4 AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Run	6 (6/1) Turkey AWG 5 (6/1) Thrush AWG 4 (6/1) Swan AWG 4 (7/1) Swanate AWG

Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-5 (6/1) Thrush AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG 5 (6/1) Thrush AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.40 in
Package Width	0.000 in

General

Color	Red
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810872208
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810872208
UPC 14 Digit GTIN	00781810872208

Logistics

Minimum Pack Quantity	25
Pallet Quantity	3200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)