



WCR33PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCR33PB](#)

WEJTAP Connector, 0.258 - 0.169 (Run), 0.230 - 0.162 (Tap),
With Red Power Booster Assembly

Features

- WEJTAP Connector
- Red Power Booster Included

Specifications

Standards - RoHS Compliance Status	NC
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	8 AWG-4 AWG
Conductor - AL Str Run	• 8 AWG • 6 AWG • 4 AWG
Conductor - AL Str Tap Range	8 AWG-4 AWG
Conductor - AL Str Tap	• 8 AWG • 6 AWG • 4 AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-5 (6/1) Thrush AWG



Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG
--------------------------	---

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Dimension - F Width Center to Center inch	1.40 in

General

Color	Red
Trade Name	WEJTAP™
UPC	781810870402
Material	Aluminum
UPC 12 Digit	781810870402
UPC 14 Digit GTIN	00781810870402

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalog \[English\]](#)