



WCR36, WEJTAP Connector

By Burndy
Catalog # [WCR36](#)

Wejtap Assembly, 0.398-0.257 (Run), 0.162-0.128 (Tap), Installed With Red Booster



Features

- WEJTAP Connector installed with Red Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	2 AWG-1/0 AWG
Conductor - AL Str Run	2 AWG 1 AWG 1/0 AWG
Conductor - AL Str Tap Range	8 AWG
Conductor - AL Str Tap	8 AWG
Conductor - ACSR Str Run Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Run	4 (7/1) Swanate AWG 3 (6/1) Swallow AWG 2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG 1 (6/1) Robin AWG 1/0 (6/1) Raven AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.40 in
Package Width	0.000 in

General

Color	Red
Trade Name	WEJTAP™
UPC	781810872352
Material	Aluminum
UPC 12 Digit	781810872352
UPC 14 Digit GTIN	00781810872352

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)