



WCR37, WEJTAP Connector

By Burndy
Catalog # [WCR37](#)

Wejtap Assembly, 0.258-0.169 (Run), 0.162-0.128 (Tap), Installed
With Red Booster

Features

- WEJTAP Connector installed with Red Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	8 AWG-4 AWG
Conductor - AL Str Run	• 8 AWG • 6 AWG • 4 AWG
Conductor - AL Str Tap Range	8 AWG
Conductor - AL Str Tap	8 AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-4 (6/1) Swan AWG
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	0.92 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.40 in
Package Width	0.000 in

General

Color	Red
Trade Name	WEJTAP™
UPC	781810872406
Material	Aluminum
UPC 12 Digit	781810872406
UPC 14 Digit GTIN	00781810872406

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)