



# WCY106PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY106PB](#)

Conn ANSI CL:AA RUS



### Features

- WEJTAP Connector
- Yellow Power Booster Included

### Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

### Conductor

|                                |                                                                                                                                                                                            |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range   | 1100 kcmil-1300 kcmil                                                                                                                                                                      |
| Conductor - AL Str Run         | <ul style="list-style-type: none"><li>• 1100 kcmil</li><li>• 1113 kcmil</li><li>• 1192 kcmil</li><li>• 1200 kcmil</li><li>• 1250 kcmil</li><li>• 1272 kcmil</li><li>• 1300 kcmil</li></ul> |
| Conductor - AL Str Tap Range   | 750 kcmil-900 kcmil                                                                                                                                                                        |
| Conductor - AL Str Tap         | <ul style="list-style-type: none"><li>• 750 kcmil</li><li>• 795 kcmil</li><li>• 800 kcmil</li><li>• 874 kcmil</li><li>• 900 kcmil</li></ul>                                                |
| Conductor Type                 | <ul style="list-style-type: none"><li>• ACSR C Str-Run</li><li>• AL C Str-Run</li><li>• ACSR C Str-Tap</li><li>• AL C Str-Tap</li></ul>                                                    |
| Conductor - ACSR Str Run Range | 1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil                                                                                                                                     |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>• 1033.5 (54/7) Curlew kcmil</li><li>• 1113 (54/19) Finch kcmil</li></ul>                                                                            |

Conductor - ACSR Str Tap Range  
Conductor - ACSR Str Tap

- 1192.5 (45/7) Bunting kcmil
- 1192.5 (54/19) Grackle kcmil
- 1272 (54/19) Pheasant kcmil
- 636 (30/19) Egret kcmil-795 (30/19) Mallard kcmil
- 636 (30/19) Egret kcmil
- 666.6 (24/7) Flamingo kcmil
- 715.5 (54/7) Crow kcmil
- 715.5 (24/7) Stilt kcmil
- 715.5 (26/7) Starling kcmil
- 715.5 (30/19) Redwing kcmil
- 795 (54/7) Condor kcmil
- 795 (26/7) Drake kcmil
- 795 (30/19) Mallard kcmil

### Configuration

|                |     |
|----------------|-----|
| Connector Type | Tap |
|----------------|-----|

### Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - G inch                        | 2.04 in |
| Dimension - F Width Center to Center inch | 3.5 in  |

### General

|                   |                |
|-------------------|----------------|
| Color             | Yellow         |
| UPC               | 781810137833   |
| Material          | Aluminum       |
| UPC 12 Digit      | 781810137833   |
| UPC 14 Digit GTIN | 00781810137833 |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

### Product Assets

[Catalog \[English\]](#)