

WCY109, WEJTAP Connector

By Burndy
Catalog # [WCY109](#)



Aluminum Overhead Wedge Tap Connector, 1.302 Dia. To 1.242 Dia. (Run), 0.953 Dia. To 0.853 Dia. (Tap)

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1100 kcmil-1300 kcmil
Conductor - AL Str Run	• 1100 kcmil • 1113 kcmil • 1192 kcmil • 1200 kcmil • 1250 kcmil • 1272 kcmil • 1300 kcmil
Conductor - AL Str Tap Range	550 kcmil-700 kcmil
Conductor - AL Str Tap	• 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run	• 1033.5 (54/7) Curlew kcmil • 1113 (54/19) Finch kcmil • 1192.5 (45/7) Bunting kcmil • 1192.5 (54/19) Grackle kcmil • 1272 (54/19) Pheasant kcmil

Conductor - ACSR Str Tap Range	477.0 (24/7) Flicker kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Tap	• 477.0 (24/7) Flicker kcmil • 477.0 (26/7) Hawk kcmil • 477. (30/7) Hen kcmil • 500.0 (30/7) Heron kcmil • 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil • 556.5 (30/7) Eagle kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	2.04 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810123683
Material	Aluminum
UPC 12 Digit	781810123683
UPC 14 Digit GTIN	00781810123683

Logistics

Minimum Pack Quantity	5
Pallet Quantity	350
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)