

WCY112, WEJTAP Connector

By Burndy
Catalog # [WCY112](#)

CONN ANSI CL:AA RUS



Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1100 kcmil-1300 kcmil
Conductor - AL Str Run	• 1100 kcmil • 1113 kcmil • 1192 kcmil • 1200 kcmil • 1250 kcmil • 1272 kcmil • 1300 kcmil
Conductor - AL Str Tap Range	300 kcmil-400 kcmil
Conductor - AL Str Tap	• 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run	• 1033.5 (54/7) Curlew kcmil • 1113 (54/19) Finch kcmil • 1192.5 (45/7) Bunting kcmil • 1192.5 (54/19) Grackle kcmil • 1272 (54/19) Pheasant kcmil

Conductor - ACSR Str Tap Range	266.8 (26/7) Partridge kcmil-397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Tap	• 266.8 (26/7) Partridge kcmil • 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	2.04 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810248409
Material	Aluminum
UPC 12 Digit	781810248409
UPC 14 Digit GTIN	00781810248409

Logistics

Minimum Pack Quantity	1
Pallet Quantity	350
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)