



# WCY112PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY112PB](#)



WEJTAP Connector, 1.302 - 1.242 (Run), 0.742 - 0.642 (Tap), With Yellow Power Booster Assembly

### Features

- WEJTAP Connector
- Yellow Power Booster Included

### Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | NC |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

### Conductor

|                                |                                                                                                                                                                                            |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range   | 1100 kcmil-1300 kcmil                                                                                                                                                                      |
| Conductor - AL Str Run         | <ul style="list-style-type: none"><li>• 1100 kcmil</li><li>• 1113 kcmil</li><li>• 1192 kcmil</li><li>• 1200 kcmil</li><li>• 1250 kcmil</li><li>• 1272 kcmil</li><li>• 1300 kcmil</li></ul> |
| Conductor - AL Str Tap Range   | 300 kcmil-400 kcmil                                                                                                                                                                        |
| Conductor - AL Str Tap         | <ul style="list-style-type: none"><li>• 300 kcmil</li><li>• 336 kcmil</li><li>• 350 kcmil</li><li>• 397 kcmil</li><li>• 400 kcmil</li></ul>                                                |
| Conductor Type                 | <ul style="list-style-type: none"><li>• ACSR C Str-Run</li><li>• AL C Str-Run</li><li>• ACSR C Str-Tap</li><li>• AL C Str-Tap</li></ul>                                                    |
| Conductor - ACSR Str Run Range | 1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil                                                                                                                                     |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>• 1033.5 (54/7) Curlew kcmil</li></ul>                                                                                                               |

Conductor - ACSR Str Tap Range  
Conductor - ACSR Str Tap

- 1113 (54/19) Finch kcmil
- 1192.5 (45/7) Bunting kcmil
- 1192.5 (54/19) Grackle kcmil
- 1272 (54/19) Pheasant kcmil
- 266.8 (26/7) Partridge kcmil-397.5 (18/1) Chickadee kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil
- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 336.4 (30/7) Oriole kcmil
- 397.5 (18/1) Chickadee kcmil

### Configuration

Connector Type Tap

### Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - G inch                        | 2.04 in |
| Dimension - F Width Center to Center inch | 3.5 in  |

### General

|                   |                |
|-------------------|----------------|
| Color             | Yellow         |
| Trade Name        | WEJTAP™        |
| UPC               | 781810036747   |
| Material          | Aluminum       |
| UPC 12 Digit      | 781810036747   |
| UPC 14 Digit GTIN | 00781810036747 |

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalog \[English\]](#)



A Hubbell brand