

# WCY114, WEJTAP Connector

By Burndy  
Catalog # [WCY114](#)

CONN ANSI CL:AA RUS



### Features

- WEJTAP Connector
- Installed with Yellow Power Booster

### Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

### Conductor

|                                |                                                                                                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range   | 1100-1400                                                                                                                                                             |
| Conductor - AL Str Run         | <ul style="list-style-type: none"><li>• 1100</li><li>• 1113</li><li>• 1192.5</li><li>• 1200</li><li>• 1272.2</li><li>• 1300</li><li>• 1351.5</li><li>• 1400</li></ul> |
| Conductor - AL Str Tap Range   | 3/0-266.8                                                                                                                                                             |
| Conductor - AL Str Tap         | <ul style="list-style-type: none"><li>• 3/0</li><li>• 4/0</li><li>• 250</li><li>• 266.8</li></ul>                                                                     |
| Conductor - ACSR Str Run Range | 1033.5 (54/7) Curlew-1272 (54/19) Pheasant                                                                                                                            |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>• 1033.5 (54/7) Curlew</li><li>• 1113 (54/19) Finch</li><li>• 1272 (54/19) Pheasant</li></ul>                                   |
| Conductor - ACSR Str Tap Range | 2/0 (6/1) Quail-266.8 (18/1) Waxwing                                                                                                                                  |
| Conductor - ACSR Str Tap       | <ul style="list-style-type: none"><li>• 2/0 (6/1) Quail</li><li>• 3/0 (6/1) Pigeon</li><li>• 4/0 (6/1) Penguin</li></ul>                                              |

- 80 (8/1) Grouse
- 101.8 (12/7) Petrel
- 110.8 (12/7) Minorca
- 134.6 (12/7) Leghorn
- 159 (12/7) Guinea
- 176.9 (12/7) Dotterel
- 190.8 (12/7) Dorking
- 211.3 (12/7) Cochin
- 203.2 (16/9) Brahma
- 266.8 (18/1) Waxwing

### Configuration

|                |     |
|----------------|-----|
| Connector Type | Tap |
|----------------|-----|

### Dimensions

|                                           |           |
|-------------------------------------------|-----------|
| Dimension - G inch                        | 2.04 in   |
| Package Height                            | 0.000 in  |
| Package Weight                            | 0.000 lb. |
| Package Length                            | 0.000 in  |
| Dimension - F Width Center to Center inch | 3.5 in    |
| Package Width                             | 0.000 in  |

### General

|                   |                |
|-------------------|----------------|
| Trade Name        | WEJTAP™        |
| UPC               | 781810056950   |
| Material          | Aluminum       |
| UPC 12 Digit      | 781810056950   |
| UPC 14 Digit GTIN | 00781810056950 |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 5   |
| Pallet Quantity       | 350 |
| Carton Quantity       | 5   |

### Product Assets

[Catalog \[English\]](#)