



WCY114PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY114PB](#)

CONN ANSI CL:AA RUS



Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run	• 1100 • 1113 • 1192.5 • 1200 • 1272.2 • 1300 • 1351.5 • 1400
Conductor - AL Str Tap	• 3/0 • 4/0 • 250 • 266.8
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run	• 1033.5 (54/7) Curlew • 1113 (54/19) Finch • 1272 (54/19) Pheasant
Conductor - ACSR Str Tap	• 2/0 (6/1) Quail

- 3/0 (6/1) Pigeon
- 4/0 (6/1) Penguin
- 80 (8/1) Grouse
- 101.8 (12/7) Petrel
- 110.8 (12/7) Minorca
- 134.6 (12/7) Leghorn
- 159 (12/7) Guinea
- 176.9 (12/7) Dotterel
- 190.8 (12/7) Dorking
- 211.3 (12/7) Cochin
- 203.2 (16/9) Brahma
- 266.8 (18/1) Waxwing

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	2.04 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
UPC	781810094518
Material	Aluminum
UPC 12 Digit	781810094518
UPC 14 Digit GTIN	00781810094518

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)