

WCY122, WEJTAP Connector

By Burndy
Catalog # [WCY122](#)

CONN ANSI CL:AA RUS



Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1272.2-1600
Conductor - AL Str Run	• 1272.2 • 1300 • 1351.5 • 1400 • 1431 • 1500 • 1590 • 1600
Conductor - AL Str Tap Range	1113-1400
Conductor - AL Str Tap	• 1113 • 1192.5 • 1272.2 • 1300 • 1351.5 • 1400
Conductor - ACSR Str Run Range	1113 (54/19) Finch-1431 (54/19) Plover
Conductor - ACSR Str Run	• 1113 (54/19) Finch

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

- 1272 (54/19) Pheasant
- 1431 (54/19) Plover
- 1033.5 (54/7) Curlew-1272 (54/19) Pheasant
- 1033.5 (54/7) Curlew
- 1113 (54/19) Finch
- 1272 (54/19) Pheasant

Configuration

Connector Type Tap

Dimensions

Dimension - G inch	2.06 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

UPC	781810094846
Material	Aluminum
UPC 12 Digit	781810094846
UPC 14 Digit GTIN	00781810094846

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)