



WCY122PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY122PB](#)

CONN ANSI CL:AA RUS



Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run	• 1272.2 • 1300 • 1351.5 • 1400 • 1431 • 1500 • 1590 • 1600
Conductor - AL Str Tap	• 1113 • 1192.5 • 1272.2 • 1300 • 1351.5 • 1400
Conductor Type	• ACSR C Str-Run • AL C Str-Run

Conductor - ACSR Str Run

Conductor - ACSR Str Tap

- ACSR C Str-Tap
- AL C Str-Tap
- 1113 (54/19) Finch
- 1272 (54/19) Pheasant
- 1431 (54/19) Plover
- 1033.5 (54/7) Curlew
- 1113 (54/19) Finch
- 1272 (54/19) Pheasant

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	2.06 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
UPC	781810094587
Material	Aluminum
UPC 12 Digit	781810094587
UPC 14 Digit GTIN	00781810094587

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)



A Hubbell brand