

WCY125, WEJTAP Connector

By Burndy
Catalog # [WCY125](#)



Aluminum Overhead Wedge Tap Connector, 1.422 Dia. To 1.314 Dia. (Run), 1.113 Dia. To 1.019 Dia. (Tap)

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

- 715.5 (26/7) Starling kcmil
- 715.5 (30/19) Redwing kcmil
- 795 (54/7) Condor kcmil
- 795 (26/7) Drake kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1300 kcmil-1500 kcmil
Conductor - AL Str Run	• 1300 kcmil • 1351 kcmil • 1400 kcmil • 1431 kcmil • 1500 kcmil
Conductor - AL Str Tap Range	900 kcmil
Conductor - AL Str Tap	900 kcmil
Conductor - ACSR Str Run Range	1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run	1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Tap Range	636 (30/19) Egret kcmil-795 (26/7) Drake kcmil
Conductor - ACSR Str Tap	• 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil • 715.5 (54/7) Crow kcmil • 715.5 (24/7) Stilt kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	2.06 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.50 in
Package Width	0.000 in

General

Color	Yellow
UPC	781810094877
Material	Aluminum
UPC 12 Digit	781810094877
UPC 14 Digit GTIN	00781810094877

Logistics

Pallet Quantity	350
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)