

WCY140, WEJTAP Connector

By Burndy
Catalog # [WCY140](#)



Aluminum Overhead Wedge Tap Connector, 1.533 Dia. To 1.471 Dia. (Run), 1.547 Dia. To 1.471 Dia. (Tap)

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1600 kcmil-1800 kcmil
Conductor - AL Str Run	• 1600 kcmil • 1700 kcmil • 1750 kcmil • 1800 kcmil
Conductor - AL Str Tap Range	1600 kcmil-1800 kcmil
Conductor - AL Str Tap	• 1600 kcmil • 1700 kcmil • 1750 kcmil • 1800 kcmil
Conductor - ACSR Str Run Range	1431 (54/19) Plover kcmil-1590 (54/19) Falcon kcmil
Conductor - ACSR Str Run	• 1431 (54/19) Plover kcmil • 1510.5 (45/7) Nuthatch kcmil • 1590 (45/7) Lapwing kcmil • 1590 (54/19) Falcon kcmil

Conductor - ACSR Str Tap Range	1431 (54/19) Plover kcmil-1590 (54/19) Falcon kcmil
Conductor - ACSR Str Tap	• 1431 (54/19) Plover kcmil • 1510.5 (45/7) Nuthatch kcmil • 1590 (45/7) Lapwing kcmil • 1590 (54/19) Falcon kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.75 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810231937
Material	Aluminum
UPC 12 Digit	781810231937
UPC 14 Digit GTIN	00781810231937

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)