



WCY140PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY140PB](#)

Conn ANSI CL:AA RUS



Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1600 kcmil-1800 kcmil
Conductor - AL Str Run	• 1600 kcmil • 1700 kcmil • 1750 kcmil • 1800 kcmil
Conductor - AL Str Tap Range	1600 kcmil-1800 kcmil
Conductor - AL Str Tap	• 1600 kcmil • 1700 kcmil • 1750 kcmil • 1800 kcmil
Conductor - ACSR Str Run Range	1431 (54/19) Plover kcmil-1590 (54/19) Falcon kcmil
Conductor - ACSR Str Run	• 1431 (54/19) Plover kcmil • 1510.5 (45/7) Nuthatch kcmil

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

- 1590 (45/7) Lapwing kcmil
- 1590 (54/19) Falcon kcmil
- 1431 (54/19) Plover kcmil-1590 (54/19) Falcon kcmil
- 1431 (54/19) Plover kcmil
- 1510.5 (45/7) Nuthatch kcmil
- 1590 (45/7) Lapwing kcmil
- 1590 (54/19) Falcon kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - F Width Center to Center inch	3.75 in
---	---------

General

Color	Yellow
UPC	781810226810
Material	Aluminum
UPC 12 Digit	781810226810
UPC 14 Digit GTIN	00781810226810

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)