



WCY145PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY145PB](#)

CONN ANSI CL:AA RUS



Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	800 kcmil-1800 kcmil
Conductor - AL Str Run	• 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil • 1033 kcmil • 1100 kcmil • 1113 kcmil • 1192 kcmil • 1200 kcmil • 1250 kcmil • 1272 kcmil • 1300 kcmil • 1351 kcmil • 1400 kcmil • 1431 kcmil • 1500 kcmil • 1590 kcmil • 1600 kcmil • 1700 kcmil • 1750 kcmil • 1800 kcmil
Conductor - AL Str Tap Range	800 kcmil-900 kcmil
Conductor - AL Str Tap	• 800 kcmil • 874 kcmil • 900 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Conductor - ACSR Str Run Range	666.6 (24/7) Flamingo kcmil-1590 (54/19) Falcon kcmil
Conductor - ACSR Str Run	• 666.6 (24/7) Flamingo kcmil • 715.5 (54/7) Crow kcmil • 715.5 (24/7) Stilt kcmil • 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil • 795 (30/19) Mallard kcmil • 874.5 (54/7) Crane kcmil • 900 (54/7) Canary kcmil • 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil • 1033.5 (54/7) Curlew kcmil • 1113 (54/19) Finch kcmil • 1192.5 (45/7) Bunting kcmil • 1192.5 (54/19) Grackle kcmil • 1272 (54/19) Pheasant kcmil • 1351.5 (54/19) Martin kcmil • 1431 (54/19) Plover kcmil • 1510.5 (45/7) Nuthatch kcmil • 1590 (45/7) Lapwing kcmil • 1590 (54/19) Falcon kcmil
Conductor - ACSR Str Tap Range	666.6 (24/7) Flamingo kcmil-795 (26/7) Drake kcmil
Conductor - ACSR Str Tap	• 666.6 (24/7) Flamingo kcmil • 715.5 (54/7) Crow kcmil • 715.5 (24/7) Stilt kcmil • 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions


Dimension - F Width Center to Center inch	3.75 in
---	---------

General

Color	Yellow
UPC	781810226827
Material	Aluminum

UPC 12 Digit	781810226827	Minimum Pack Quantity	1
UPC 14 Digit GTIN	00781810226827		

Logistics



Product Assets

[Catalog \[English\]](#)