

WCY48, WEJTAP Connector

By Burndy
Catalog # [WCY48](#)



Wejtap connector installed with yellow booster, .537-.750 (Run),
.162-.204 (Tap)

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	4/0 AWG-450 kcmil
Conductor - AL Str Run	• 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil
Conductor - AL Str Tap Range	8 AWG-4 AWG
Conductor - AL Str Tap	• 8 AWG • 6 AWG • 4 AWG
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Run	• 4/0 (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil

- 203.2 (16/9) Brahma kcmil
- 266.8 (18/1) Waxwing kcmil
- 266.8 (26/7) Owl kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil
- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 336.4 (30/7) Oriole kcmil
- 397.5 (18/1) Chickadee kcmil
- 397.5 (24/7) Brant kcmil
- 397.5 (26/7) Ibis kcmil
- 6 (6/1) Turkey AWG-5 (6/1) Thrush AWG
 - 6 (6/1) Turkey AWG
 - 5 (6/1) Thrush AWG

Conductor - ACSR Str Tap
Range
Conductor - ACSR Str Tap

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.37 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810873809
Material	Aluminum
UPC 12 Digit	781810873809
UPC 14 Digit GTIN	00781810873809

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)