



WCY49PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY49PB](#)



Wejtap connector installed with Yellow booster, .537-.750 Run, .203-.271 (Tap)

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	4/0 AWG-450 kcmil
Conductor - AL Str Run	• 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Run	• 4/0 (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil

- 203.2 (16/9) Brahma kcmil
- 266.8 (18/1) Waxwing kcmil
- 266.8 (26/7) Owl kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil
- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 336.4 (30/7) Oriole kcmil
- 397.5 (18/1) Chickadee kcmil
- 397.5 (24/7) Brant kcmil
- 397.5 (26/7) Ibis kcmil
- 6 (6/1) Turkey AWG-3 (6/1) Swallow AWG
- 6 (6/1) Turkey AWG
- 5 (6/1) Thrush AWG
- 4 (6/1) Swan AWG
- 4 (7/1) Swanate AWG
- 3 (6/1) Swallow AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.37 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870433
Material	Aluminum
UPC 12 Digit	781810870433
UPC 14 Digit GTIN	00781810870433

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)