

WCY50, WEJTAP Connector

By Burndy
Catalog # [WCY50](#)



Wejtap Assembly, Installed With Yellow Booster, Sum of diameters: 1.069 (Max), .860 (Min)

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	4/O AWG-450 kcmil
Conductor - AL Str Run	4/O AWG 250 kcmil 266 kcmil 300 kcmil 336 kcmil 350 kcmil 397 kcmil 400 kcmil 450 kcmil
Conductor - AL Str Tap Range	4 AWG-1/O AWG
Conductor - AL Str Tap	4 AWG 3 AWG 2 AWG 1 AWG 1/O AWG
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap
Conductor - ACSR Str Run Range	4/O (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Run	4/O (6/1) Penguin AWG 80 (8/1) Grouse kcmil 101.8 (12/7) Petrel kcmil 110.8 (12/7) Minorca kcmil 134.6 (12/7) Leghorn kcmil 159 (12/7) Guinea kcmil 176.9 (12/7) Dotterel kcmil 190.8 (12/7) Dorking kcmil

Conductor - ACSR Str Tap Range	4 (7/1) Swanate AWG-1 (6/1) Robin AWG
Conductor - ACSR Str Tap	4 (7/1) Swanate AWG 3 (6/1) Swallow AWG 2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG 1 (6/1) Robin AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.37 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810873908
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810873908
UPC 14 Digit GTIN	00781810873908

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10



A Hubbell brand