



WCY52PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY52PB](#)



Wejtap connector installed with Yellow booster, .537-.750 Run, .364-.588 (Tap)

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	4/0-450
Conductor - AL Str Run	• 4/0 • 250 • 266.8 • 300 • 336.4 • 350 • 397.5 • 400 • 450
Conductor - AL Str Tap Range	1-266.8
Conductor - AL Str Tap	• 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin-397.5 (26/7) Ibis
Conductor - ACSR Str Run	• 4/0 (6/1) Penguin • 80 (8/1) Grouse • 101.8 (12/7) Petrel • 110.8 (12/7) Minorca • 134.6 (12/7) Leghorn • 159 (12/7) Guinea • 176.9 (12/7) Dotterel • 190.8 (12/7) Dorking • 211.3 (12/7) Cochin • 203.2 (16/9) Brahma • 266.8 (18/1) Waxwing

Conductor - ACSR Str Tap Range	• 266.8 (26/7) Owl • 266.8 (26/7) Partridge • 300.0 (26/7) Ostrich • 336.4 (18/1) Merlin • 336.4 (26/7) Linnet • 336.4 (30/7) Oriole • 397.5 (18/1) Chickadee • 397.5 (24/7) Brant • 397.5 (26/7) Ibis
Conductor - ACSR Str Tap	1 (6/1) Robin-266.8 (18/1) Waxwing
	• 1 (6/1) Robin • 1/0 (6/1) Raven • 2/0 (6/1) Quail • 3/0 (6/1) Pigeon • 4/0 (6/1) Penguin • 80 (8/1) Grouse • 101.8 (12/7) Petrel • 110.8 (12/7) Minorca • 134.6 (12/7) Leghorn • 159 (12/7) Guinea • 176.9 (12/7) Dotterel • 190.8 (12/7) Dorking • 211.3 (12/7) Cochin • 203.2 (16/9) Brahma • 266.8 (18/1) Waxwing

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.37 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870464
Material	Aluminum
UPC 12 Digit	781810870464
UPC 14 Digit GTIN	00781810870464

Logistics

Minimum Pack Quantity	1
-----------------------	---



A Hubbell brand