



# WCY57PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY57PB](#)



Wejtap Assembly, 336.4-600 kcmil (Run), 4-1 AWG (Tap), Wiring taps

### Features

- WEJTAP Connector, packaged with Yellow Power Booster

### Application

For use in tap applications using large run and tap conductor sizes

### Specifications

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | NC |
| Buy American Compliant             | No |
| EU RoHS Indicator                  | No |
| Certification - CSA Approved       | No |

### Conductor

|                                |                                                                                                                                                                                           |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range   | 336.4-600                                                                                                                                                                                 |
| Conductor - AL Str Run         | <ul style="list-style-type: none"><li>• 336.4</li><li>• 350</li><li>• 397.5</li><li>• 400</li><li>• 450</li><li>• 477</li><li>• 500</li><li>• 550</li><li>• 556.5</li><li>• 600</li></ul> |
| Conductor - AL Str Tap Range   | 4-1                                                                                                                                                                                       |
| Conductor - AL Str Tap         | <ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li></ul>                                                                                                   |
| Conductor Type                 | <ul style="list-style-type: none"><li>• ACSR C Str-Run</li><li>• AL C Str-Run</li><li>• ACSR C Str-Tap</li><li>• AL C Str-Tap</li></ul>                                                   |
| Conductor - ACSR Str Run Range | 300.0 (26/7) Ostrich-556.5 (24/7) Parakeet                                                                                                                                                |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>• 300.0 (26/7) Ostrich</li><li>• 336.4 (18/1) Merlin</li><li>• 336.4 (26/7) Linnet</li><li>• 336.4 (30/7) Oriole</li></ul>                          |

- 397.5 (18/1) Chickadee
- 397.5 (24/7) Brant
- 397.5 (26/7) Ibis
- 397.5 (30/7) Larkspur
- 477.0 (18/1) Pelican
- 477.0 (24/7) Flicker
- 477.0 (26/7) Hawk
- 477.0 (30/7) Hen
- 556.5 (24/7) Parakeet
- 4 (7/1) Swanate-1 (6/1) Robin
- 4 (7/1) Swanate
- 3 (6/1) Swallow
- 2 (6/1) Sparrow
- 2 (7/1) Sparate
- 1 (6/1) Robin

### Configuration

|                |     |
|----------------|-----|
| Connector Type | Tap |
|----------------|-----|

### Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - G inch                        | 1.53 in |
| Dimension - F Width Center to Center inch | 3 in    |

### General

|                   |                               |
|-------------------|-------------------------------|
| Color             | Yellow                        |
| Trade Name        | WEJTAP™                       |
| Sub Brand         | WEJTAP                        |
| UPC               | 781810870518                  |
| Type              | Wejtap Connector with Booster |
| Material          | Aluminum                      |
| UPC 12 Digit      | 781810870518                  |
| UPC 14 Digit GTIN | 00781810870518                |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### Product Assets

[Catalog \[English\]](#)