

WCY59, WEJTAP Connector

By Burndy
Catalog # [WCY59](#)



Wejtap Connector With Power Booster Assembly, 12.63 IN L, 6.38 IN W, 0.666-0.893 (Run), 0.162-0.199(Tap), Installed With Yellow Booster

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	336.4-600
Conductor - AL Str Run	336.4 350 397.5 400 450 477 500 550 556.5 600
Conductor - AL Str Tap Range	6-4
Conductor - AL Str Tap	6 4
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich-556.5 (24/7) Parakeet
Conductor - ACSR Str Run	300.0 (26/7) Ostrich 336.4 (18/1) Merlin 336.4 (26/7) Linnet

- 336.4 (30/7) Oriole
- 397.5 (18/1) Chickadee
- 397.5 (24/7) Brant
- 397.5 (26/7) Ibis
- 397.5 (30/7) Larkspur
- 477.0 (18/1) Pelican
- 477.0 (24/7) Flicker
- 477.0 (26/7) Hawk
- 477.0 (30/7) Hen
- 556.5 (24/7) Parakeet
- 6 (6/1) Turkey

Conductor - ACSR Str Tap Range	
Conductor - ACSR Str Tap	6 (6/1) Turkey

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810874356
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810874356
UPC 14 Digit GTIN	00781810874356

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)