



WCY59PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY59PB](#)



WEJTAP Connector, 0.893 - 0.666 (Run), 0.199 - 0.162 (Tap),
With Yellow Power Booster Assembly

Features

- WEJTAP Connector, packaged with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Standards - RoHS Compliance	NC
Status	
Buy American Compliant	No
EU RoHS Indicator	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	336.4-600
Conductor - AL Str Run	336.4 350 397.5 400 450 477 500 550 556.5 600
Conductor - AL Str Tap Range	6-4
Conductor - AL Str Tap	6 4
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich-556.5 (24/7) Parakeet
Conductor - ACSR Str Run	300.0 (26/7) Ostrich 336.4 (18/1) Merlin 336.4 (26/7) Linnet

- 336.4 (30/7) Oriole
- 397.5 (18/1) Chickadee
- 397.5 (24/7) Brant
- 397.5 (26/7) Ibis
- 397.5 (30/7) Larkspur
- 477.0 (18/1) Pelican
- 477.0 (24/7) Flicker
- 477.0 (26/7) Hawk
- 477.0 (30/7) Hen
- 556.5 (24/7) Parakeet
- 6 (6/1) Turkey

Conductor - ACSR Str Tap Range	6 (6/1) Turkey
Conductor - ACSR Str Tap	6 (6/1) Turkey

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810870532
Type	Wejtap Connector with Booster
Material	Aluminum
UPC 12 Digit	781810870532
UPC 14 Digit GTIN	00781810870532

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)