



# WCY61PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY61PB](#)



Wejtap Tap Connector, 397.5-477 Std 477-636 18/1 Cmpct,450-556.5 Std, 477-636 Cmpct Al&Cu (Run), 477 Std. 556.5-636 18/1 Cmpct, 477-556.5 Std, 550-636 cmpct Al&Cu (Tap).

## Features

- WEJTAP Connector, packaged with Yellow Power Booster

## Application

For use in tap applications using large run and tap conductor sizes

## Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | NC |
| Buy American Compliant             | No |
| Certification - cULus              | No |
| EU RoHS Indicator                  | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

## Conductor

|                              |                                                                                                                                                                                             |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range | 350-700                                                                                                                                                                                     |
| Conductor - AL Str Run       | <ul style="list-style-type: none"><li>350</li><li>397.5</li><li>400</li><li>450</li><li>477</li><li>500</li><li>550</li><li>556.5</li><li>600</li><li>636</li><li>650</li><li>700</li></ul> |
| Conductor - AL Str Tap Range | 336.4-700                                                                                                                                                                                   |
| Conductor - AL Str Tap       | <ul style="list-style-type: none"><li>336.4</li><li>350</li><li>397.5</li><li>400</li><li>450</li><li>477</li><li>500</li><li>550</li><li>556.5</li><li>600</li><li>636</li></ul>           |

|                                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Type                 | <ul style="list-style-type: none"><li>650</li><li>700</li><li>ACSR C Str-Run</li><li>AL C Str-Run</li><li>ACSR C Str-Tap</li><li>AL C Str-Tap</li></ul>                                                                                                                                                                                                                                                                                                                                                   |
| Conductor - ACSR Str Run Range | 336.4 (18/1) Merlin-556.5 (30/7) Eagle                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>336.4 (18/1) Merlin</li><li>336.4 (26/7) Linnet</li><li>336.4 (30/7) Oriole</li><li>397.5 (18/1) Chickadee</li><li>397.5 (24/7) Brant</li><li>397.5 (26/7) Ibis</li><li>397.5 (30/7) Larkspur</li><li>477.0 (18/1) Pelican</li><li>477.0 (24/7) Flicker</li><li>477.0 (26/7) Hawk</li><li>477.0 (30/7) Hen</li><li>556.5 (24/7) Parakeet</li><li>556.5 (26/7) Dove</li><li>556.5 (30/7) Eagle</li></ul>                                                             |
| Conductor - ACSR Str Tap Range | 266.8 (26/7) Partridge-556.5 (30/7) Eagle                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Conductor - ACSR Str Tap       | <ul style="list-style-type: none"><li>266.8 (26/7) Partridge</li><li>300.0 (26/7) Ostrich</li><li>336.4 (18/1) Merlin</li><li>336.4 (26/7) Linnet</li><li>336.4 (30/7) Oriole</li><li>397.5 (18/1) Chickadee</li><li>397.5 (24/7) Brant</li><li>397.5 (26/7) Ibis</li><li>397.5 (30/7) Larkspur</li><li>477.0 (18/1) Pelican</li><li>477.0 (24/7) Flicker</li><li>477.0 (26/7) Hawk</li><li>477.0 (30/7) Hen</li><li>556.5 (24/7) Parakeet</li><li>556.5 (26/7) Dove</li><li>556.5 (30/7) Eagle</li></ul> |

## Configuration

|                |     |
|----------------|-----|
| Connector Type | Tap |
|----------------|-----|

## Dimensions

|                               |                               |                                                            |                |
|-------------------------------|-------------------------------|------------------------------------------------------------|----------------|
| Dimension - G inch            | 1.53 in                       | Material                                                   | Aluminum       |
| Dimension - F Width Center to | 3 in                          | UPC 12 Digit                                               | 781810870556   |
| Center inch                   |                               | UPC 14 Digit GTIN                                          | 00781810870556 |
| <b>General</b>                |                               | <b>Logistics</b>                                           |                |
| Color                         | Yellow                        | Minimum Pack Quantity                                      | 5              |
| Trade Name                    | WEJTAP™                       | <b>Product Assets</b><br><a href="#">Catalog [English]</a> |                |
| Sub Brand                     | WEJTAP                        |                                                            |                |
| UPC                           | 781810870556                  |                                                            |                |
| Type                          | Wejtap Connector with Booster |                                                            |                |



A Hubbell brand