



WCY64PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY64PB](#)



Wejtap Assembly, 600 kcmil-1000 kcmil (Run), 600 kcmil-1000 kcmil (Tap)

Features

- WEJTAP Connector, packaged with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Standards - RoHS Compliance	NC
Status	
Buy American Compliant	No
EU RoHS Indicator	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	

- 350 kcmil
- 397 kcmil
- 400 kcmil
- 450 kcmil
- 477 kcmil
- 500 kcmil
- 550 kcmil
- 556 kcmil
- 600 kcmil
- 636 kcmil
- 650 kcmil
- 700 kcmil

Conductor - AL Str Tap Range	2/O AWG-300 kcmil
Conductor - AL Str Tap	

- 2/O AWG
- 3/O AWG
- 4/O AWG
- 250 kcmil
- 266 kcmil
- 300 kcmil

Conductor Type	
	• ACSR C Str-Run
	• AL C Str-Run
	• ACSR C Str-Tap
	• AL C Str-Tap

Conductor - ACSR Str Run Range	336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil
--------------------------------	--

Conductor - ACSR Str Run	
	• 336.4 (18/1) Merlin kcmil
	• 336.4 (26/7) Linnet kcmil
	• 336.4 (30/7) Oriole kcmil
	• 397.5 (18/1) Chickadee kcmil

Conductor - ACSR Str Tap Range	
Conductor - ACSR Str Tap	

- 397.5 (24/7) Brant kcmil
- 397.5 (26/7) Ibis kcmil
- 397.5 (30/7) Larkspur kcmil
- 477.0 (18/1) Pelican kcmil
- 477.0 (24/7) Flicker kcmil
- 477.0 (26/7) Hawk kcmil
- 477. (30/7) Hen kcmil
- 500.0 (30/7) Heron kcmil
- 556.5 (24/7) Parakeet kcmil
- 556.5 (26/7) Dove kcmil
- 556.5 (30/7) Eagle kcmil

1/O (6/1) Raven AWG-300.0 (26/7) Ostrich kcmil

- 1/O (6/1) Raven AWG
- 2/O (6/1) Quail AWG
- 3/O (6/1) Pigeon AWG
- 4/O (6/1) Penguin AWG
- 80 (8/1) Grouse kcmil
- 101.8 (12/7) Petrel kcmil
- 110.8 (12/7) Minorca kcmil
- 134.6 (12/7) Leghorn kcmil
- 159 (12/7) Guinea kcmil
- 176.9 (12/7) Dotterel kcmil
- 190.8 (12/7) Dorking kcmil
- 211.3 (12/7) Cochin kcmil
- 203.2 (16/9) Brahma kcmil
- 266.8 (18/1) Waxwing kcmil
- 266.8 (26/7) Owl kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions


Dimension - G inch	1.53 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810870587
Type	Wejtap Connector with Booster
Material	Aluminum

UPC 12 Digit	781810870587	Minimum Pack Quantity	10
UPC 14 Digit GTIN	00781810870587		

Logistics



Product Assets

[Catalog \[English\]](#)