



WCY65PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY65PB](#)



WEJTAP Connector, 0.940 - 0.683 (Run), 0.562 - 0.382 (Tap),
With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	• 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil
Conductor - AL Str Tap Range	1/0 AWG-250 kcmil
Conductor - AL Str Tap	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run	• 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil

Conductor - ACSR Str Tap Range

Conductor - ACSR Str Tap

- 397.5 (26/7) Ibis kcmil
 - 397.5 (30/7) Larkspur kcmil
 - 477.0 (18/1) Pelican kcmil
 - 477.0 (24/7) Flicker kcmil
 - 477.0 (26/7) Hawk kcmil
 - 477. (30/7) Hen kcmil
 - 500.0 (30/7) Heron kcmil
 - 556.5 (24/7) Parakeet kcmil
 - 556.5 (26/7) Dove kcmil
 - 556.5 (30/7) Eagle kcmil
- 1 (6/1) Robin AWG-4/0 (6/1) Penguin AWG
- 1 (6/1) Robin AWG
 - 1/0 (6/1) Raven AWG
 - 2/0 (6/1) Quail AWG
 - 3/0 (6/1) Pigeon AWG
 - 4/0 (6/1) Penguin AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870594
Material	Aluminum
UPC 12 Digit	781810870594
UPC 14 Digit GTIN	00781810870594

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand